



LaserTrace 3 H₂O LaserTrace 3 O₂ Ultra-High Purity Gas Analyzers

AUTOMOTIVE

ENERGY

ENVIRONMENTAL

GASES & CHEMICALS

LABORATORIES

LEDS

SEMICONDUCTORS

Designed for trace level contamination analysis,
the LaserTrace 3 H₂O and O₂ analyzers offer:

- Industry-leading parts-per-trillion detection capability
- Unprecedented speed of response
- Widest available dynamic range
- Absolute measurement (freedom from calibration gases)
- Flexibility: up to four (4) measurement points per electronics module
- Extremely low cost of ownership
- Electronics module compatible with existing LaserTrace sensor modules

Delivering your best measurements

Detect gas quality upsets before they can damage your processes. Using Tiger Optics' LaserTrace 3 H₂O and O₂ analyzers, you can verify moisture and oxygen impurity levels with part-per-trillion accuracy, drift-free stability, and virtually immediate response. You'll find our system exceptionally easy and fast to install, and effortless to

maintain, with built-in zero verification. It measures in bulk gases, specialty gases, and gas mixtures. And its robust design – free of moving parts – results in an analyzer that has a high Mean Time Between Failure (MTBF) rate and a very low Cost of Ownership (CoO).

Tigeroptics

21ST CENTURY SPECTROSCOPY

LaserTrace 3 H₂O

LaserTrace 3 O₂

Ultra-High Purity Gas Analyzers



Winner Golden Gas Award

Tiger Optics' LaserTrace 3 is *Gases & Instrumentation's* 2012 Golden Gas Award Winner, in recognition of its technological innovativeness, superior specifications, cost benefits and other quality considerations as determined by independent industry experts.

Performance	
Operating range	See table below
Detection Limit (LDL, 24 hr. peak-to-peak variation)	See table below
Sensitivity (3 σ)	See table below
Precision (1 σ , greater of)	$\pm 0.75\%$ or $\frac{1}{3}$ of Sensitivity
Accuracy (greater of)	$\pm 3\%$ or $\frac{1}{2}$ of LDL
Speed of response	< 3 minutes to 95%
Environmental conditions	10°C – 40°C, 30 – 80% RH (non-cond)
Storage temperature	-10°C – 50°C

Gas Handling System and Conditions

Wetted materials	316L stainless steel (optional Hastelloy [®]) 10 Ra surface finish
Gas connections	$\frac{1}{4}$ " male VCR inlet and outlet
Leak tested to	1×10^{-9} mbar l / sec
Inlet pressure	15 – 125 psig (2.0 – 9.6 bara)
Flow rate	0.5 – 1.8 slpm (gas dependent)
Sample gases	Most inert, toxic, passive and corrosive matrices
Gas temperature	Up to 60°C

Dimensions	H x W x D [inches (mm)]
Electronics unit	14 x 19 x 14 (356 x 483 x 356)
Sensor rack	8.75 x 19 x 27 (222 x 483 x 686)
Standard sensor	7 x 4.75 x 27 (178 x 121 x 686)
O ₂ sensor	8.75 x 12.9 x 27 (222 x 328 x 686)

Weight

Electronics unit	32 lbs (14.5 kg)
Standard sensor	38 lbs (17.2 kg)
O ₂ sensor	60.5 lbs (27.5 kg)

Electrical

Alarm indicators	User programmable setpoints (1 per sensor), Form-C relay
Power requirements	90-240 VAC 50/60 Hz
Power consumption	200 Watts max.
Signal output	0-5 VDC, isolated 0-20 or 4-20 mA output per sensor
User interface	10.4" color VGA display/Touchscreen PS/2 mouse and keyboard connection 10/100/1000BaseT Ethernet 2 USB ports, RS-232

	Performance: Trace H ₂ O			Trace O ₂		
	Range	LDL	Sensitivity	Range	LDL	Sensitivity
In Nitrogen	0-10 ppm	250 ppt	200 ppt	0-5 ppm	125 ppt	100 ppt
In Helium	0-2 ppm	100 ppt	50 ppt	0-1 ppm	50 ppt	25 ppt
In Argon	0-5 ppm	110 ppt	90 ppt	0-2.5 ppm	55 ppt	45 ppt
In Hydrogen	0-8 ppm	180 ppt	150 ppt	0-4 ppm	90 ppt	75 ppt
In Oxygen	0-5 ppm	130 ppt	100 ppt		n/a	

Contact us for additional analytes and matrices.
Vacuum source required for some applications
U. S. Patent # 5,528,040 • U.S. Patent # 7,255,836 • Other patents pending

TigerOptics, LLC

250 Titus Avenue, Warrington, PA 18976
Phone +1 (215) 343 6600 • Fax +1 (215) 343 4194
Sales@tigeroptics.com • www.tigeroptics.com

Tigeroptics

21ST CENTURY SPECTROSCOPY